

## Quattroflow™ QF2500

New Multiple-Use and Single-Use Pump Size Available

With a maximum flow rate of 2,500 lph, the new Quattroflow™ QF2500 pumps are located between the existing QF1200 (max. 1,200 lph) and QF4400 (max. 5,000 lph) pump sizes.

The complete Quattroflow pump range covers a flow capacity between 0.06 and 16,000 lph with eight pump sizes now available – the right Quattroflow pump for all applications.

The QF2500 pumps offer the following main features and benefits:

- · New pump chamber design (patent pending), available as Multiple-Use and Single-Use model
- · Self-draining design
- Up to 125:1 turn-down ratio
- Linear flow performance
- 50-2,500 lph flow range, max. 4/6 bar (58/87 psi)
- · High flow stability even at low flow rates
- · Clean-In-Place (CIP), Steam-In-Place (SIP), autoclavable
- · Available accessories: Control box, power box, diaphragm sensor, PID pressure controller
- Typical applications include: Chromatography, TFF, virus filtration, sterile filtration, depth filtration

QF2500 Quaternary Diaphragm Pump

Ouattroflow<sup>™</sup> has extended the Multiple-Use and Single-Use product lines of Quaternary (Four-Piston) Diaphragm Pumps with the new QF2500 size pumps.



Quattroflow develops and manufactures, in close cooperation with its customers, specific Quaternary (Four-Piston) Diaphragm Pumps for critical applications in the pharmaceutical and biotech industries. The method of operation of Quattroflow pumps allows them to gently, safely and securely convey aqueous solutions and biological products that are sensitive to shear force. The four-piston design does not feature a mechanical shaft seal or wetted rotating parts, ensuring total product containment without abrasion. Additionally, the four-piston pumping principle enables risk-free dry-running, low pulsation, self priming, and minimal particle generation.












## Quattroflow<sup>™</sup>QF2500

Flow Rate Maximum:		
Eccentric Shaft 5°	2,500 lph (41 lpm)	
Flow Rate Minimum:		
Eccentric Shaft 5°	50 lph (0.8 lpm)	
Pressure:		
Temperature of Fluid $<$ 40 $^{\circ}$ C (104 $^{\circ}$ F) MU/SU	6/4 bar (87/58 psi)	
Temperature of Fluid $>$ 40 $^{\circ}$ C (104 $^{\circ}$ F)	4 bar (58 psi)	
Maximum Temperature:		
Fluid MU/SU	80/60°C (176/140°F)	
CIP MU only	90°C (194°F)	
Autoclave	130°C (260°F)	
Pump Speed Range:		
rpm	30-1,750	
Suction Lift Dry at Maximum Speed:		
Eccentric Shaft 5°	4-4.5 m (13.1-14.7 ft)	
Volume Specifications:		
Approximated Volume per Revolution at Free Output	27 ml	
Approximated Filling Volume Without Connectors	210 ml	
Connection Specification (Standard):		
Connectors	1" TC	
Position of Connectors	Front	

MU = Stainless steel pump chamber (Multiple-Use), SU = Plastic pump chamber (Single-Use)	e)
--	----

Product Wetted Materials (Standard):		
Pump Chamber MU/SU	SS316L/PP	
Valve Plate MU/SU	SS316L/PP	
Diaphragms	TPE	
Valves	EPDM	
0-rings	EPDM	
Certificates/Proofs (Optional):		
Elastomer (product wetted)	USP <88> CI. VI; FDA21CFR177; BSE/TSE Safe	
Stainless Steel Parts (product wetted)	3.1; Surface Roughness; Ferrite Content	
Motor:		
Rated speed @ 50Hz	1,445 min-1	
Voltage	230/400 V	
Power	1.5 kW	
Pump Dimension with Motor and Housing:		
Length	815 mm (32.09")	
Width	215 mm (8.46")	
Height	295 mm (11,61")	
Pump Weight with Motor and Housing:		
MU	63 kg (139 lb.)	
SU	56 kg (123 lb.)	





Almatec reserves the right to modify the information and illustrations contained in this document without prior notice. This is a non-contractual document. 03-2020.

Authorized PSG® Partner:

ALMATEC Maschinenbau GmbH Hochstraße 150-152 47228 Duisburg, Germany Tel: +49 (2065) 89205-0 • Fax: +49 (2065) 89205-40 info@almatec.de



